



Destemmers and crushers - Respect of the grapes



Destemmers and crushers Delta E / F

Gentle processing

Poured into the hopper, the grapes are then gradually and gently conveyed according to a pre-set destemming speed. In this zone, the cage has no holes and clusters are taken by the beater fingers without bursting the berries or grinding them.

In the destemming zone, the holes of the electropolished stainless steel cage have been designed with deep and round edges (5 mm for E2 and E4, 6,5 mm for E6 and E8). The shaft is equipped with paddles whose extremity is enlarged and rubberized (E2 and E4) or in stainless steel (E6 and E8). The stress applied on the grapes is therefore better distributed. The berries remain intact, the stems progress easily along the cage.

The cage and the beater rotate in the same direction, avoiding the grapes shearing effects.

In the destemming area, the paddles number is doubled for E2 and E4. Part of those paddles can be dismounted, one out of two for example for E2 and E4. The length of destemming area is then adjustable according to the grape variety and grape maturity. Destemming is more efficient, without excessive beating of the stems.

All the driving elements are grouped in a rear tilting unit that are totally separated from the berries and juice circulation area and do not disturb handlings that can be made around the destemmer.

Multi purposes

Three models of cage, adapted to the average berry diameter thus to the grape variety, are available. They can be easily and rapidly changed.

The rotating speed of the separating unit (beater + cage) is adjustable and can be controlled through an electronic variator (E2 and E4).

The machine installation is very easy. The destemmer can be set on a support, giving entire access to the lower part of the machine, or can be fixed on wheels.

The wheels leave enough space for the pump to be set under the destemmer (E2 and E4).

Hygiene

The washing of the machine is carried out thanks to rotative water guns located at the upper part of the cage. The electropolished cage makes the washing easier. Indeed the specific treatment of the stainless steel limits the grip of materials (Potassium bitartrate, colour...). Side covers allow access to the cage, to the beater and to the evacuation hopper making the checking of the washing quality easier.

Maintenance and security

Handlings and adjustments are easy. The access to the separating elements is made possible by simply lifting the rear part.

The changing of the cage and the beater can be rapidly carried out.

The security is also important. Any handling of the side covers or the rear tilting unit stops the machine automatically.



Standard hopper













Interchangeable cages

Rotative water guns

Open destemmer for a better access

Delta F2 crusher

Draining hopper

Options

Crusher

Articulated on a vertical axis, the crusher can be put aside in case of no crushing (F2-F4).

The rollers spacing is adjustable without particular tool. Milled buttons make easier the adjustment of crushing. Rollers are made with a high resistant polymer material. For more security, rollers are retractable.

Draining hopper

If the grapes flow is not regulated by a screw hopper or if the grapes are mechanically harvested and very juicy, it is necessary to regulate the feeding of the destemmer:

To do so, you can use the Delta draining hopper:

- The perforated part based at the bottom of the hopper releases free juices and avoids disruptions caused by the juice flow.
- The hopper feeding screw regulates the grapes flow at the nominal output of the machine.

PEHD cage

The High density polyethylen cage is available with a hole diameter of 22 and 25 mm and is approximately 8 mm thick (E2-E4). Holes are rounded in the inner and outer part of the cage (Bucher Vaslin patent) in order to keep the berries intact and prevent from undesirable substances and bits of stems to be released.



PEHD cage







Pumps

For each destemmer of the Delta E range or for each crusher of the Delta F range corresponds a PMV helicoidal rotor pump: E2/F2/PMV2 – E4/F4/PMV4 – E6/FC6/PMV6 – E8/FC8/PMV8.

Dimensions and technical data





Peace of mind - a Bucher Vaslin Guarantee.

A worldwide network of distributors authorized by Bucher Vaslin provides a local field service. All products are manufactured by the company. World leader in the pressing equipment, Bucher Vaslin can supply you with spare parts for 20 years. The CE marking certifies that tank presses are in conformity with European Directives. Bucher Vaslin S.A. is an ISO 9001: 2015 and OHSAS 18001: 2007 company registered through Bureau Veritas.



Delta E4 / F4



Delta E2 / F2 / PMV2

Distributed by: Bucher Vaslin

Rue Gaston Bernier - BP 70028 F - 49290 Chalonnes sur Loire Tel. +33 (0)2 41 74 50 50 Fax +33 (0)2 41 74 50 51

E-mail: commercial@buchervaslin.com